

### Characteristics



HEPA Included



Pharmaceutical Applications



Cleanroom Applications



Accessories Included



Activated Carbon



Wet & Dry Applications



High Efficiency



Mercury Recovery



MRV-15 AIR (STD) Shown

- HEPA Filter - Included with an efficiency of 99.995% on 0.3 micron. Tested: IEST RP-CC001.3. H14 by MPPS method as per EN 1822.
- \*Cleanroom compatible. Can be used in the pharmaceutical industry
- Designed for mercury recovery
- Pneumatically (air) operated
- Wet & dry recovery
- Available with a high-density polyethylene recovery tank
- EMI/RFI shielded
- Available with a timer (hour counter)
- Includes Mersorb® brand activated carbon for the adsorption of mercury vapors
- Includes a suction hose, mercury separator and jars with lids
- based on a 4-wheel dolly

High-density polyethylene recovery tank. This unit contains a true HEPA Filter (H14) located upstream of the motor. This unit is designed for mercury recovery and includes a Mersorb® brand activated carbon for the adsorption of mercury vapors. A mercury separator and jars with lids are included. Includes a timer (hour counter). This unit is EMI/RFI shielded. All of our HEPA/ULPA vacuum cleaner are Aerosol Leak Tested before leaving our facility.

## Specifications for model MRV-15 AIR (STD)

## Compressor Specifications

Name	Part Number	Wet Recovery	Paper Bag Capacity	Dry Recovery	Vacuum Pressure	Air Flow	Venturi	Ideal Compress or HP	Input Air Pressur	Aire Line Size	Input Air Volume
MRV-15 AIR (STD)	110807	76 L	19 L	38 L	4318 mm H <sub>2</sub> O	51.9 L/s	Single Venturi with 6 mm airjet	15 HP	80 PSI / 1160.3 Bar	1/2"	21.2 L/s
Dimensions: N/A Weight: 0 Kg Noise Level: 0.00 dB(A)											

### EMI - EMI Suppresion / RFI Shielding

These cleanroom vacuum cleaners are equipped with an electronic filter suppresser which reduces electromagnetic interference (EMI), both radiated and conducted, below class B limits for digital apparatus as established by the FCC and ISO. It also provides shielding against RFI (Radio Frequency Interference). The electronic filter is wired in line with the motor. If the electronic filter should fail, power to the motor will automatically be cut-off. These vacuum cleaners will not disrupt computers, radio and video monitors and other sensitive electronic equipment.

### HEPA - High Efficiency Particulate Air Filter

A HEPA filter is a type of air filter, which means it filters the air coming in or out of the vacuum cleaner system. It can remove at least 99.99% of dust, pollen, mould, bacteria and any other airborne particles with a size of 0.3 micron or larger.

North-America: Each HEPA Filter has a minimum filtration efficiency of 99.99% on 0.3 micron. Tested as per IES-RP-CC001.3.

Europe: Each HEPA Filter has a minimum filtration efficiency of 99.995% on 0.3 micron, rated H14 as per EN 1822 by MPPS method.

### ULPA - Ultra Low Penetration Air Filter

A ULPA filter is a type of air filter. It can remove at least 99.999% of dust, pollen, mould, bacteria and any other airborne particles with a size of 0.12 microns or larger.

North-America: Each ULPA Filter has a minimum filtration efficiency of 99.999% on 0.12 micron. Tested as per IES-RP-CC001.3.

Europe: Each ULPA Filter has a minimum filtration efficiency of 99.9995% on 0.18 micron, rated U15 as per EN 1822 by MPPS method.

## Tools & Accessories

### ACTIVATED CARBON CARTRIDGE - Included

Part#	Quantity	Description
212200C	1	CARBON CARTRIDGE ASSEMBLY WITH 3mm MERSORB (FOR MERCURY VAPORS)

### ACTIVATED CARBON CARTRIDGE - Optional

Part#	Quantity	Description
212200B	1	CARBON CARTRIDGE ASSEMBLY WITH 3mm CARBON (REGULAR)
212200K	1	CARBON CARTRIDGE ASSEMBLY WITH 3mm KOGC3/KINA3 CARBON (FOR CHLORIDE VAPORS)
212200L	1	CARBON CARTRIDGE ASSEMBLY WITH 3mm A-3 CARBON (FOR ARSINE AND PHOSPHINE VAPORS)

### MERCURY RECOVERY SEPARATOR AND ACCESSORIES - Included

Part#	Quantity	Description
212208	1	MERCURY SEPARATOR -STAINLESS STEEL(INCLUDES 2 MERCURY RECOVERY JARS AND (2) LIDS FOR JAR)
212210	1	JAR FOR MERCURY RECOVERY 20oz(540 ml) WITH LID
212211	1	CLEAR SUCTION HOSE ASSEMBLY 1"(25.4mm)x8"(20.3cm) FOR USE WITH MERCURY SEPARATOR



**Arc Technologies**

Worldwide Technology For Controlled Environments

Web site: [www.arctechnologies.co.uk](http://www.arctechnologies.co.uk)

email: [achambers@arctechnologies.co.uk](mailto:achambers@arctechnologies.co.uk)

Tel: +(44)0115 928 1508

**TOOLS AND ACCESSORIES - Included**

Part#	Quantity	Description
212215	1	CLEAR URETHANE SUCTION HOSE ASSEMBLY 10'(3m)WITH 1.5"(38mm) FEMALE CAMLOCK(PVC) ON ONE END
381092	1	DRAIN HOSE ASSEMBLY 0.75"(19mm)x5'(1.5m)CLEAR HOSE WITH 0.75"(19mm) PVC FEMALE CAMLOCK
211787	1	AIR SUPPLY HOSE ASSEMBLY STANDARD TYPE Ø0.5"(12.7mm)x50'(15m)W/1 MALE QUICK DISC&1 FEMALE QUICK DIS
381197	1	CREVICE TOOL 11" (27.9cm) -GREY PVC
381207	1	REDUCER/ADAPTOR Ø1.5" TO Ø1.25" (Ø38mm TO Ø32mm) PVC
323312	1	ROUND BRUSH Ø1.25"(32mm)
323314	1	UPHOLSTERY FLAT TOOL Ø1.25"(32mm) PVC
381380	1	FLOOR TOOL 14" ABS WITH NYLON BRUSHES
381381	1	FLOOR TOOL 14" ABS w/SQUEEGEE
381382	1	REPLACEMENT SQUEEGEE BLADES (SET) FOR 14" FLOOR TOOL (ABS & ALUMINUM)
381351A	1	WAND PVC DOUBLE BEND 54" w/ ABS AMERICAN ATTACHMENT

**Warning:**

Do not use these vacuum cleaners to recover explosive dusts or flammable liquids



# Arc Technologies

Worldwide Technology For Controlled Environments

Web site: [www.arctechnologies.co.uk](http://www.arctechnologies.co.uk)

email: [achambers@arctechnologies.co.uk](mailto:achambers@arctechnologies.co.uk)

Tel: +(44)0115 928 1508